

SENCITY® Omni-S Slim 3x3 Wi-Fi MIMO

1399.17.0208

Properties

- Small omni-directional MIMO antenna for Wi-Fi + LTE 2600 applications
- Dual band Wi-Fi / WLAN and LTE 2600 3 x 3 MIMO antenna
- Supports the 2.4 GHz and 5 GHz and LTE 2.5 to 2.7 GHz bands
- Three ports each with broad-band antenna radiator technology
- IEEE 802.11 b/g/a/h/p and 802.11 n / ac
- For industrial indoor environment - IP65 protected



Electrical data		
	Band 1	Band 2
Frequency	2400 MHz ... 2690 MHz	5150 MHz ... 5935 MHz
Impedance	50 Ω	50 Ω
VSWR	1.7	1.7
Gain	5 dBi	6 dBi
HPBW vertical	65 °	65 °
HPBW horizontal	360 °	360 °
Isolation between Ports	20 dB	20 dB
Ambient Temperature	25 °C	25 °C
Composite Power max	50 W	30 W

Electrical remarks

Remarks	Three cable pigtails with connector N (male) directly attached to the antenna body
---------	--

Ports

	Port 1	Port 2	Port 3
Connector	N, plug (male)	N, plug (male)	N, plug (male)
Cable type	S_04262_D-09	S_04262_D-09	S_04262_D-09
Cable length	0.9 m	0.9 m	0.9 m

SENCITY® Omni-S Slim 3x3 Wi-Fi MIMO

1399.17.0208

Ports			
	Port 1	Port 2	Port 3
Polarization	vertical	vertical	vertical
DC grounded	Yes	Yes	Yes

Connections			
	Port 1	Port 2	Port 3
Band 1	✓	✓	✓
Band 2	✓	✓	✓

Mechanical data	
Weight	0.6 kg
Dimensions	32 mm x 282 mm x 92 mm (Height x Width x Depth)

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 9010 (white)
Back plate/base plate material	Aluminum

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Indoor
Ingress protection (IP Rating)	IP65

Environmental remarks	
Vibration and mechanical shock: ETSI EN 300-19-2-3 T3.3	
Flammability rating antenna radome: UL 94 V0 / RF pigtail cable: UL 1581 § 1080 (VW-I)	
UV protection antenna: UL746C f1 / RF pigtail cable: ISO 4892-2A	

Ordering information		
Item description	Item number	Product name
1399.17.0208	84076853	SENCITY® Omni-S Slim 3x3 Wi-Fi MIMO

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3260 / Date of publication: 13.08.2025 / uncontrolled copy