

SENCITY® Tram MULTI Antenna

1399.99.0245

Properties

- Rugged vehicle rooftop multi-band antenna for Light Rail
- Supports TETRA, LTE450, 2G/3G/4G/5G cellular, Wifi 2.4/5 GHz, Wifi 6E and Dual Band GNSS (Beidou, Galileo, GPS, Glonass)
- 6 separate ports for 1x TETRA/cellular and 4x4 Wifi MIMO plus GNSS
- Meets EN50155 railway standard
- Fire retardant acc. to EN45545-2 and NFPA-130
- Single hole mounting, easy cabling feed-through



Electrical data				
	Band 1	Band 2	Band 3	Band 4
Name	TETRA/LTE450	Cellular	Cellular	Cellular
Frequency	380 MHz ... 470 MHz	617 MHz ... 960 MHz	1350 MHz ... 2700 MHz	3300 MHz ... 4200 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2.5	2.1	2.1	2.1
Gain	3 dBi	2 dBi	4 dBi	4 dBi
Isolation between Ports				
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	40 W

	Band 5	Band 6	Band 7	Band 8
Name	Cellular	WiFi	WiFi	GNSS
Frequency	4900 MHz ... 7125 MHz	2400 MHz ... 2500 MHz	4900 MHz ... 7125 MHz	1164 MHz ... 1279 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2.1	2.1	2.1	1.5
Gain	5 dBi	6 dBi	6 dBi	
Isolation between Ports		20 dB	20 dB	
Ambient Temperature	25 °C	25 °C	25 °C	

SENCITY® Tram MULTI Antenna

1399.99.0245

	Band 5	Band 6	Band 7	Band 8
Composite Power max	40 W	30 W	30 W	

	Band 9
Name	GNSS
Frequency	1559 MHz ... 1610 MHz
Impedance	50 Ω
VSWR	1.8
Gain	
Isolation between Ports	
Ambient Temperature	
Composite Power max	

Electrical remarks

Remarks	Ground plane: Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger and Isolation is provided as typical values. Indicated VSWR values are mostly valid for installations on non-metallic surfaces also (no specific ground plane requirements). Indicated gain values will be achieved on a metallic ground plane of 1 x 1 m or larger.
---------	--

Ports			
	Port 1	Port 2 to 5	Port 6
Port name	Tetra 1 (yellow)	WiFi 1-4 (blue)	GNSS (black)
Connector	SMA, plug (male)	SMA, plug (male)	TNC, plug (male)
Cable type	RADOX_RF_316_D	RADOX_RF_316_D	RADOX_RF_316_D
Cable length	0.3 m	0.3 m	0.3 m
Polarization	vertical	vertical	circular right
DC grounded	Yes	Yes	No

Connections

	Port 1	Port 2 to 5	Port 6
Port name	Tetra 1 (yellow)	WiFi 1-4 (blue)	GNSS (black)
Band 1	✓		
Band 2	✓		
Band 3	✓		
Band 4	✓		
Band 5	✓		
Band 6		✓	
Band 7		✓	
Band 8			✓
Band 9			✓

Electrical data LNA

LNA is connected to	Port 6
Input voltage	3 V ... 5 V
Current consumption	45 mA
Noise figure	2 dB

SENCITY® Tram MULTI Antenna

1399.99.0245

Electrical data LNA			
Total gain @90° elevation		42 dBic	
Mechanical data			
Weight		1.1 kg	
Dimensions		60 mm x 210 mm (Height x Diameter)	
Mounting breakthrough		Ø 30 mm	
Material data			
Radome material		PC (Polycarbonate)	
Radome colour		RAL 9017 (black)	
Back plate/base plate material		Aluminum	
Environmental data			
Operation temperature		-40 °C ... 85 °C	
Storage temperature		-40 °C ... 85 °C	
Transport temperature		-40 °C ... 85 °C	
Environment (application)		Outdoor	
Ingress protection (IP Rating)		IP68, IP69k	
Flammability rating		EN 45545-2 NFPA-130	
Solar radiation		DIN 75220	
Environmental remarks			
Environmental tests: EN50155:2018-05			
High-voltage protection: EN50124-1:2017-03			
Low corrosion designed acc. to MIL-F-14072D			
This Antenna is compliant with the Radio Equipment Directive 2014/53/EU			
Ordering information			
Item description		Item number	Product name
1399.99.0245		85185526	SENCITY® Tram MULTI Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35311 / Date of publication: 21.07.2025 / uncontrolled copy