


SENCITY® Road IC MIMO Antenna

1399.19.0189

Properties

- Supports 6x6 MIMO for Wi-Fi and ready for Wi-Fi 6E
- Single hole mounting, low profile and vandalism proof.
- Works without metal ground plane
- ISO 16750, ECE-R118 compliant
- 0.5m of cable and SMA connector
- Supports 6x6 Cellular MIMO in 2.3 / 2.6 / 3.5 GHz bands.



Electrical data

	Band 1	Band 2	Band 3	Band 4
Frequency	2300 MHz ... 2500 MHz	2500 MHz ... 2690 MHz	3400 MHz ... 4200 MHz	4900 MHz ... 5975 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	2	2.5	2.5
Gain	5 dBi	5 dBi	6 dBi	6.5 dBi
Isolation between Ports	12 dB	12 dB	20 dB	20 dB
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	30 W

	Band 5
Frequency	5975 MHz ... 7125 MHz
Impedance	50 Ω
VSWR	2.5
Gain	6.5 dBi
Isolation between Ports	20 dB
Ambient Temperature	25 °C
Composite Power max	20 W

Ports

	Port 1 to 6
Port name	Cell / Wi-Fi 1 to 6 (white)
Connector	SMA, plug (male)
Cable type	ENVIROFLEX_178-AM

SENCITY® Road IC MIMO Antenna

1399.19.0189

Ports	
	Port 1 to 6
Cable length	0.1 m
Polarization	vertical
DC grounded	Yes

Connections	
	Port 1 to 6
Port name	Cell / WiFi 1 to 6 (white)
Band 1	✓
Band 2	✓
Band 3	✓
Band 4	✓
Band 5	✓

Mechanical data	
Weight	0.9 kg
Dimensions	33.2 mm x 145 mm (Height x Diameter)
Mounting breakthrough	Ø 30 mm

Material data	
Radome material	Reinforced PC (Polycarbonate)
Radome colour	RAL 7044 (grey)

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	IP68, IP69
Flammability rating	ECE-R118
Solar radiation	DIN 75220

Environmental remarks	
Environmental tests: ISO 16750:2010	
CE-Mark	

Ordering information	
Item number	Item description
85191789	1399.19.0189

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35209 / Date of publication: 15.01.2025 / uncontrolled copy