


**COAXIAL CONNECTOR, SMC, 50 Ohm, Right angle cable plug (male)**

16\_SMC-50-2-10/111\_N

**Properties**

- Screw-on mechanism permits a vibration-proof connection
- Suitable for semi-permanent connections and for use in mobile equipment
- Applicable in frequencies up to 10 GHz

**Product configuration**

|                |        |                                         |
|----------------|--------|-----------------------------------------|
| Interface type | Gender | Standard                                |
| SMC            | plug   | IEC 60169-9_MIL-STD-348A/312_CECC 22140 |

**Interface and material data**

| Piece parts     | Material               | Plating                                    |
|-----------------|------------------------|--------------------------------------------|
| Centre contact  | Copper Beryllium Alloy | Gold Plating (Nickel underplated)          |
| Outer conductor | Brass                  | Gold Plating (Nickel underplated)          |
| Body            | Brass                  | Gold Plating (Nickel underplated)          |
| Insulator       | PFA / PTFE             |                                            |
| Coupling nut    | Brass                  | Gold Plating (Nickel underplated)          |
| Crimp ferrule   | Copper                 | Gold Plating (without Nickel underplating) |

**Electrical data**

|                     |             |
|---------------------|-------------|
| Impedance           | 50 $\Omega$ |
| Interface frequency | 10 GHz      |

**Mechanical data**

|                            |           |
|----------------------------|-----------|
| Weight                     | 0.0038 kg |
| Mating cycles              | 500       |
| Cable entry centre contact | crimped   |
| Cable entry outer contact  | crimped   |

**Environmental data**

|                       |                   |
|-----------------------|-------------------|
| Operation temperature | -65 °C ... 165 °C |
|-----------------------|-------------------|

**COAXIAL CONNECTOR, SMC, 50 Ohm, Right angle cable plug (male)**

16\_SMC-50-2-10/111\_N

| Material compliance |                                   |                                 |                      |
|---------------------|-----------------------------------|---------------------------------|----------------------|
| Item number         | Directive / Regulation            | Rating                          | Exemptions / Details |
| 22640269            | RoHS 2011/65/EU and (EU) 2015/863 | Compliant with exemption        | 6c                   |
|                     | REACH 1907/2006 Article 33 SVHC   | Contains one or more SVHC >0,1% | CAS: 7439-92-1 Lead  |
| 22645323            | RoHS 2011/65/EU and (EU) 2015/863 | Compliant with exemption        | 6c                   |
|                     | REACH 1907/2006 Article 33 SVHC   | Contains one or more SVHC >0,1% | CAS: 7439-92-1 Lead  |

| Ordering Information Table |                       |                |
|----------------------------|-----------------------|----------------|
| Item number                | Item description      | Packaging type |
| 22640269                   | 16_SMC-50-2-10/111_NE | Single         |
| 22645323                   | 16_SMC-50-2-10/111_NH | Bulk 100 pcs   |

| Suitable cables   |                    |
|-------------------|--------------------|
| Cable group       | U2 - 2 mm / 50 Ohm |
| Suitable cables   | RG_316_/U          |
|                   | RG_188_A/U         |
| Additional cables | RG_174_/U          |

| Additional Information |    |
|------------------------|----|
| Only as assembly       | No |

| Suitable tools |                  |               |
|----------------|------------------|---------------|
| Item number    | Item description | Type of tool  |
| 23004027       | 74_Z-0-0-352     | Torque wrench |
| 22660188       | 74_Z-0-0-343     | Assembly tool |

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P2991 / Date of publication: 11.07.2025 / uncontrolled copy