

SENCITY® SC OMNI-M Antenna

1399.99.0337

Properties

- Rugged omni-directional antenna for installation on outdoor cabinets
- Supports TETRA, LTE450, 2G/3G/4G/5G cellular, Wifi 2.4/5 GHz, Wifi 6E and Dual Band GNSS (Beidou, Galileo, GPS, Glonass)
- 6 separate ports for 1x TETRA/cellular and 4x4 Wifi MIMO plus GNSS
- Meets ETSI 300 019-1-4 class 4.1E
- Low profile housing
- Single hole mounting, easy cabling feed-through



Electrical data				
	Band 1	Band 2	Band 3	Band 4
Name	TETRA/LTE450	Cellular	Cellular	Cellular
Frequency	380 MHz ... 470 MHz	694 MHz ... 960 MHz	1350 MHz ... 2700 MHz	3300 MHz ... 4200 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2.5	2	2	2
Gain	3 dBi	2 dBi	4 dBi	4 dBi
Isolation between Ports				
Ambient Temperature	25 °C	25 °C	25 °C	25 °C
Composite Power max	40 W	40 W	40 W	40 W

	Band 5	Band 6	Band 7	Band 8
Name	Cellular	WiFi	WiFi	GNSS
Frequency	4900 MHz ... 7125 MHz	2400 MHz ... 2500 MHz	4900 MHz ... 7125 MHz	1164 MHz ... 1279 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	2	2	1.5
Gain	5 dBi	6 dBi	6 dBi	
Isolation between Ports		20 dB	20 dB	
Ambient Temperature	25 °C	25 °C	25 °C	
Composite Power max	40 W	30 W	30 W	

SENCITY® SC OMNI-M Antenna

1399.99.0337

	Band 9
Name	GNSS
Frequency	1559 MHz ... 1610 MHz
Impedance	50 Ω
VSWR	1.8
Gain	
Isolation between Ports	
Ambient Temperature	
Composite Power max	

Electrical remarks

Remarks	Ground plane: Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger and Isolation is provided as typical values. Indicated VSWR values are mostly valid for installations on non-metallic surfaces also (no specific ground plane requirements). Indicated gain values will be achieved on a metallic ground plane of 1 x 1 m or larger.
---------	--

Ports			
	Port 1	Port 2 to 5	Port 6
Port name	Tetra 1 (yellow)	WiFi 1-4 (blue)	GNSS (black)
Connector	TNC, plug (male)	N, jack (female)	TNC, plug (male)
Cable type	ENVIROFLEX_316_D	ENVIROFLEX_316_D	ENVIROFLEX_316_D
Cable length	0.5 m	0.5 m	0.5 m
Polarization	vertical	vertical	circular right
DC grounded	Yes	Yes	No

Connections

	Port 1	Port 2 to 5	Port 6
Port name	Tetra 1 (yellow)	WiFi 1-4 (blue)	GNSS (black)
Band 1	✓		
Band 2	✓		
Band 3	✓		
Band 4	✓		
Band 5	✓		
Band 6		✓	
Band 7		✓	
Band 8			✓
Band 9			✓

Electrical data LNA

LNA is connected to	Port 6
Input voltage	3 V ... 5 V
Current consumption	45 mA
Noise figure	2 dB
Total gain @90° elevation	42 dBic

SENCITY® SC OMNI-M Antenna

1399.99.0337

Mechanical data	
Weight	1.1 kg
Dimensions	60 mm x 210 mm (Height x Diameter)
Mounting breakthrough	Ø 30 mm

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7044 (light grey)
Back plate/base plate material	Aluminium

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP68, IP69k
Solar radiation	DIN 75220

Environmental remarks	
Environmental tests: ETSI 300 019-4-2 class 4.1E	
Low corrosion designed acc. to MIL-F-14072D	

Ordering information		
Item description	Item number	Product name
1399.99.0337	85185568	SENCITY® SC OMNI-M Antenna

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35416 / Date of publication: 13.06.2025 / uncontrolled copy