

COAXIAL CONNECTOR, C, 50 Ohm, Straight cable jack (female)

21_C-50-7-3/122_N

Properties

- Easy coupling and decoupling
- Applicable in frequencies up to 11 GHz



Product configuration		
Interface type	Gender	Standard
C	jack	IEC 60169-7_MIL-STD-348A/302

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data	
Weight	0.0365 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	clamped

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, C, 50 Ohm, Straight cable jack (female)

21_C-50-7-3/122_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22543427	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22543427	21_C-50-7-3/122_NE	Single

Suitable cables	
Cable group	U33 - 7 mm / 50 Ohm
	U32 - 7 mm / 50 Ohm
	U29 - 7 mm / 50 Ohm
Suitable cables	RG_393_/U
	RG_214_/U
	GX_07272_D

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543126	74_Z-0-0-16	Spanner

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2912 / Date of publication: 11.07.2025 / uncontrolled copy