

SENCITY® Road MULTI Antenna

1399.99.0417

Properties

- Supports Wifi 2.4/5 GHz, Wifi 6E and Dual Band GNSS (Beidou, Galileo, GPS, Glonass)
- 7 separate ports for 6x6 Wifi MIMO plus GNSS
- Fire retardant acc. to ECE-R118
- Single hole mounting, easy cabling feed-through
- Meets ISO16750 automotive standard



Electrical data				
	Band 1	Band 2	Band 3	Band 4
Name	WiFi	WiFi	GNSS	GNSS
Frequency	2400 MHz ... 2500 MHz	4900 MHz ... 7125 MHz	1559 MHz ... 1610 MHz	1559 MHz ... 1610 MHz
Impedance	50 Ω	50 Ω	50 Ω	50 Ω
VSWR	2	2	1.8	1.8
Gain	6 dBi	6 dBi		
Isolation between Ports	24 dB	24 dB		
Ambient Temperature	25 °C	25 °C		
Composite Power max	30 W	30 W		

Electrical remarks	
Remarks	Ground plane: Indicated VSWR values are valid for a metallic ground plane of 0.5 x 0.5m or larger and Isolation is provided as typical values. Indicated VSWR values are mostly valid for installations on non-metallic surfaces also (no specific ground plane requirements). Indicated gain values will be achieved on a metallic ground plane of 1 x 1 m or larger.

Ports		
	Port 1 to 8	Port 9
Port name	WiFi 1-8 (blue)	GNSS (black)
Connector	SMA, plug (male)	TNC, plug (male)
Cable type	ENVIROFLEX_316_D-AM	ENVIROFLEX_316_D-AM
Cable length	0.3 m	0.3 m
Polarization	vertical	circular right

SENCITY® Road MULTI Antenna

1399.99.0417

Ports		
	Port 1 to 8	Port 9
DC grounded	Yes	No

Connections		
	Port 1 to 8	Port 9
Port name	WiFi 1-8 (blue)	GNSS (black)
Band 1	✓	
Band 2	✓	
Band 3		✓
Band 4		✓

Electrical data LNA	
LNA is connected to	Port 5
Input voltage	3 V ... 5 V
Current consumption	45 mA
Noise figure	2 dB
Total gain @90° elevation	42 dBic

Mechanical data	
Weight	1.1 kg
Dimensions	60 mm x 210 mm (Height x Diameter)
Mounting breakthrough	Ø 30 mm

Material data	
Radome material	PC (Polycarbonate)
Radome colour	RAL 7043 (dark grey)
Back plate/base plate material	Aluminium

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Transport temperature	-40 °C ... -40 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP68, IP69k
Flammability rating	ECE-R118
Solar radiation	DIN 75220

Environmental remarks
Environmental tests: ISO 16750:2012/2010
Low corrosion designed acc. to MIL-F-14072D
ECE-R10
E-Mark

Ordering information		
Item description	Item number	Product name
1399.99.0417	85192485	SENCITY® Road MULTI Antenna

SENCITY® Road MULTI Antenna

1399.99.0417

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P35235 / Date of publication: 11.08.2025 / uncontrolled copy