

COAXIAL CONNECTOR, QN, 50 Ohm, Straight bulkhead receptacle, jack (female)

22_QN-50-0-1/133_N

Properties

- Same performance but smaller than N-Interface
- High packing density
- Applicable in frequencies up to 11 GHz
- Easy to mate - No torque or tooling required



Product configuration		
Interface type	Gender	Standard
QN	jack	QN QLF compliant
Interface and material data		
Piece parts	Material	Plating
Centre contact	Bronze	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Electrical data		
Impedance	50 Ω	
Interface frequency	11 GHz	
Mechanical data		
Weight	0.012 kg	
Mating cycles	100	
Flange type	round flange / others	
Tab style	Standard	
Environmental data		
Operation temperature	-40 °C ... 125 °C	

COAXIAL CONNECTOR, QN, 50 Ohm, Straight bulkhead receptacle, jack (female)
22_QN-50-0-1/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23033904	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
23033904	22_QN-50-0-1/133_NY		Tray

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2787 / Date of publication: 12.07.2025 / uncontrolled copy