


COAXIAL CONNECTOR, QN, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_QN-50-0-1/133_N

Properties

- Same performance but smaller than N-Interface
- High packing density
- Applicable in frequencies up to 11 GHz
- Easy to mate - No torque or tooling required



Product configuration		
Interface type	Gender	Standard
QN	jack	QN QLF compliant

Interface and material data		
Piece parts	Material	Plating
Centre contact	Bronze	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data	
Weight	0.0131 kg
Mating cycles	100
Flange type	square flange / 17.5 X 17.5
Tab style	solder end

Environmental data	
Operation temperature	-40 °C ... 125 °C

COAXIAL CONNECTOR, QN, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_QN-50-0-1/133_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23033251	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
23033252	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23033251	23_QN-50-0-1/133_NE	Single
23033252	23_QN-50-0-1/133_NY	Tray

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2722 / Date of publication: 12.07.2025 / uncontrolled copy