


# COAXIAL CONNECTOR, SMA, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23\_SMA-50-0-272/133\_N

## Properties

- Excellent return loss
- Intermateable with PC3.5 and SK
- Applicable in frequencies up to 18 GHz



Product configuration		
Interface type	Gender	Standard
SMA	jack	IEC 60169-15_MIL-STD-348A/310_CECC 22110
Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Electrical data		
Impedance	50 Ω	
Interface frequency	18 GHz	
Mechanical data		
Weight	0.002 kg	
Mating cycles	500	
Flange type	square flange / 12.7 X 12.7	
Tab style	Standard	
Environmental data		
Operation temperature	-65 °C ... 165 °C	

**COAXIAL CONNECTOR, SMA, 50 Ohm, Straight panel receptacle, jack (female), flange mount**

23\_SMA-50-0-272/133\_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23030310	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23030310	23_SMA-50-0-272/133_NH	Bulk 100 pcs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P2704 / Date of publication: 12.07.2025 / uncontrolled copy