

COAXIAL CONNECTOR, UHF, X Ohm, Straight cable jack (female)

21_UHF-0-7-4/033_

Properties

- Mateable with 4 mm banana plugs
- Applicable in frequencies up to 200 MHz

**Product configuration**

Interface type	Gender	Standard
UHF	jack	IEC 60169-12

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data

Interface frequency	0.2 GHz
---------------------	---------

Mechanical data

Weight	0.0324 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data

Operation temperature	-55 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, UHF, X Ohm, Straight cable jack (female)

21_UHF-0-7-4/033_

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22542775	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table	
Item number	Item description
22542775	21_UHF-0-7-4/033_-E

Suitable cables	
Cable group	U42 - 7 mm / 50 Ohm
	U29 - 7 mm / 50 Ohm
Suitable cables	RG_213_/U
	GX_07272
Additional cables	G_07272
	RADOX_RF_213

Additional Information	
Only as assembly	No

Suitable tools		
Item number	Item description	Type of tool
22543196	76_Z-0-7-7	Crimping dies
22543195	76_Z-0-7-1	Crimping dies
22543189	76_Z-0-4-1	Crimping dies
22543185	76_Z-0-3-1	Crimping dies

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2825 / Date of publication: 11.07.2025 / uncontrolled copy