

COAXIAL CONNECTOR, 4.3-10, 50 Ohm, Straight panel receptacle, jack (female), flange mount

23_4310-50-0-16/003_-

Properties

- Excellent PIM and RL independent of torque
- Compact size (25.4mm flange)
- Applicable in frequencies up to 12 GHz
- 40% lower weight and size than 7/16
- IEC Standardized



Product configuration

Interface type	Gender	Standard
4.3-10	jack	IEC 61169-54

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Silver Plating
Outer conductor	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	12 GHz

Mechanical data

Weight	0.064381 kg
Mating cycles	100
Flange type	square flange / 25.4 X 25.4
Tab style	solder end

Environmental data

Operation temperature	-55 °C ... 90 °C
-----------------------	------------------

COAXIAL CONNECTOR, 4.3-10, 50 Ohm, Straight panel receptacle, jack (female),
flange mount

23_4310-50-0-16/003_-

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85064166	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
85064166	23_4310-50-0-16/003_-Y		Tray

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2756 / Date of publication: 12.07.2025 / uncontrolled copy