


32041E-29171SVCR3-29094CR-6, VITA 67.3 SMPS (female), SMA (male), 50 Ohm, 26.5 GHz, 6 in, 152.4 mm

32041E-29171SVCR3-29094CR-6

Properties

- Assembly with VITA 67.3 compliant SMPS connector
- Part of the "bend-to-the-end" MINIBEND product family
- Direct replacement for 047 size Semi-Rigid cables
- Compliant to MIL-DTL-17 (cable) and MIL-PRF-39012 (connectors)
- Applicable up to 26.5 GHz



Product configuration

Configuration type	One pair of assemblies
Type of cable	MICROBEND R (32041E)
Type description connector A	29171SVCR3-32-41
Series connector A	SMPS, straight - jack
Type description connector B	29094CR-32-41
Series connector B	SMA, straight - plug
Length	152.4 mm
Length	6 inch
Length type	REF to REF

Electrical data

Impedance	50 Ω
Max. operating frequency	26.5 GHz
VSWR max	1.5
Max. insertion loss	2.07 dB
Propagation velocity	70.3 %

Electrical Data (frequency related)

Frequency range	Return loss	VSWR max	Insertion loss
0 GHz ... 2 GHz	21.66 dB	1.18	0.4 dB
2 GHz ... 12 GHz	16.53 dB	1.35	1.2 dB
12 GHz ... 18 GHz	15.56 dB	1.4	1.56 dB
18 GHz ... 26.5 GHz	13.97 dB	1.5	2.07 dB

32041E-29171SVCR3-29094CR-6, VITA 67.3 SMPS (female), SMA (male), 50 Ohm, 26.5 GHz, 6 in, 152.4 mm

32041E-29171SVCR3-29094CR-6

Mechanical data	
Weight	24 g
Cable diameter	1.96 mm
Static bending radius	1.52 mm
Environmental data	
Operation temperature	-55 °C ... 125 °C
Ordering information	
Item number	Item description
85259449	32041E-29171SVCR3-29094CR-6

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P58473 / Date of publication: 18.08.2025 / uncontrolled copy