

COAXIAL ADAPTER, N - 716, 50 Ohm, plug / plug (male / male)

32_N-716-50-1/---_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
N	plug (male)	IEC 61169-16_MIL-STD-348A/304_CECC 22210
7/16	plug (male)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data		
N		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
7/16		
Piece parts	Material	Plating
Centre contact	Brass	Silver Plating
Outer conductor	Brass	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz
VSWR	DC - 7.5 GHz ($\leq 1.03 + 0.02 f \text{ GHz}$)

COAXIAL ADAPTER, N - 716, 50 Ohm, plug / plug (male / male)
32_N-716-50-1/---_N

Mechanical data	
Weight	0.1061 kg
Mating cycles	500

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22544576	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22544576	32_N-716-50-1/---_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2307 / Date of publication: 12.07.2025 / uncontrolled copy