

COAXIAL ADAPTER, QN - 7/16, 50 Ohm, jack / jack (female / female)

31_QN-716-50-1/113_W

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
QN	jack (female)	QN QLF compliant
7/16	jack (female)	IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Interface and material data		
QN		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
7/16		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	7.5 GHz

Mechanical data	
Weight	0.0656 kg
Mating cycles	100

COAXIAL ADAPTER, QN - 7/16, 50 Ohm, jack / jack (female / female)

31_QN-716-50-1/113_W

Environmental data	
Operation temperature	-40 °C ... 125 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23033269	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23033269	31_QN-716-50-1/113_WE	Single

Additional Information	
Remarks	3rd order passive intermodulation max.: static -165 dBc typ.

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2373 / Date of publication: 12.07.2025 / uncontrolled copy