

COAXIAL ADAPTER, BNC - TNC, 50 Ohm, plug / jack (male / female)

33_BNC-TNC-50-1/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
BNC	plug (male)	IEC 61169-8_MIL-STD-348A/301_CECC 22120
TNC	jack (female)	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data

BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
TNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPLATE (R) Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

COAXIAL ADAPTER, BNC - TNC, 50 Ohm, plug / jack (male / female)
33_BNC-TNC-50-1/133_N

Electrical Data (frequency related)			
Frequency range		Return loss	VSWR
0 GHz ... 4 GHz		20 dB	1.22
Mechanical data			
Weight		0.0207 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-65 °C ... 165 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22540614	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22540614	33_BNC-TNC-50-1/133_NE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2236 / Date of publication: 12.07.2025 / uncontrolled copy