

COAXIAL ADAPTER, MBX - SMA, 50 Ohm, plug / jack (male / female)

33_MBX-SMA-50-1/111_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
MBX	plug (male)	HUBER+SUHNER MBX
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CEEC 22110

Interface and material data		
MBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPRO Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPLATE (R) Plating
Body	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 6 GHz	28 dB	1.083

COAXIAL ADAPTER, MBX - SMA, 50 Ohm, plug / jack (male / female)

33_MBX-SMA-50-1/111_N

Mechanical data	
Weight	0.002215 kg
Mating cycles	500

Environmental data	
Operation temperature	-55 °C ... 155 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84093656	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84093656	33_MBX-SMA-50-1/111_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2232 / Date of publication: 12.07.2025 / uncontrolled copy