

COAXIAL ADAPTER, SMB - SMA, 50 Ohm, plug / jack (male / female)

33_SMB-SMA-50-1/111_U

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
SMB	plug (male)	IEC 60169-10_MIL-STD-348A/311_CECC 22130
SMA	jack (female)	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Interface and material data		
SMB		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
SMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz
VSWR	DC - 4 GHz ($\leq 1.05 + 0.04 f \text{ GHz}$)

Mechanical data	
Weight	0.0054 kg
Mating cycles	500

COAXIAL ADAPTER, SMB - SMA, 50 Ohm, plug / jack (male / female)

33_SMB-SMA-50-1/111_U

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22641727	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description	Packaging type
22641727	33_SMB-SMA-50-1/111_UE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P2143 / Date of publication: 12.07.2025 / uncontrolled copy