

COAXIAL ADAPTER, TNC Quick-mate - N, 50 Ohm, plug / jack (male / female)

33_TNC-N-Q50-4/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
TNC Quick-mate	plug (male)	HUBER+SUHNER Quick-mate
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
TNC Quick-mate		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 4 GHz	30 dB	1.065
4 GHz ... 8 GHz	24 dB	1.12
8 GHz ... 11 GHz	18 dB	1.28

COAXIAL ADAPTER, TNC Quick-mate - N, 50 Ohm, plug / jack (male / female)
33_TNC-N-Q50-4/133_N

Mechanical data		
Weight	0.0361 kg	
Mating cycles	500	
Environmental data		
Operation temperature	-65 °C ... 165 °C	
Ordering Information Table		
Item number	Item description	Packaging type
22660360	33_TNC-N-Q50-4/133_NE	Single
Additional Information		
Remarks	Durability of QUICK MATE interface: 1000 matings	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2137 / Date of publication: 27.05.2024 / uncontrolled copy