


COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology

3400.17.0380

Properties

- Maintenance-free products
- Highest current handling capability up to 100 kA max.
- Best PIM performance
- Available in several frequency ranges from 380MHz up until 18GHz



Product configuration	
Main path connectors	Port 1: unprotected, N jack (female) Port 2: protected, N jack (female)
Mounting and grounding	MH69 (bulkhead mounting)
Side of bulkhead	protected side
Inline design	YES
EMP can be install reversed	YES

Interface and material data	
Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)
	Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Frequency frame	6000 MHz to 18000 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.3 dB
CW power frame	≤ 100 W
Peak power frame	≤ 1000 W
Residual pulse energy (typ.)	600 nJ (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s)
Residual pulse voltage (typ.)	2 V (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s)
Surge current handling capability	50 kA multiple (test pulse 8/20 μ s)

Electrical remarks	
Gas tube	No DC / shorted QW or LC

COAXIAL SURGE PROTECTOR DEVICE, Quarter-wave stub technology

3400.17.0380

Mechanical data	
Weight	202 g
Mating cycles	500

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP65, according to IEC 60529
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. A
Moisture resistance according	MIL-STD-202, Method 106

Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23034973	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Comment	
NATO Stock Number	6625-01-642-5282

Ordering Information Table	
Item number	Item description
23034973	3400.17.0380

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2069 / Date of publication: 28.02.2025 / uncontrolled copy