

COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 3 GHz (Platform 3000), with GDT 230 V

3402.17.3003

Properties

- Broadband frequency operation from DC to 3 GHz
- Gas discharge tube replaceable and included
- DC/AC remote powering via coaxial same cable
- Surge current handling capability 30 kA once and 20 kA multiple
- Semper self-extinguishing functionality optional


CE **UK** **CA**

Product configuration

Main path connectors	Port 1: unprotected, N jack (female) Port 2: protected, N jack (female)
Mounting and grounding	MH170 (bulkhead mounting)
Side of bulkhead	protected side
EMP can be install reversed	YES

Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Copper Beryllium Alloy / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

Electrical data

Impedance	50 Ω
Frequency frame	0 MHz to 3000 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.3 dB
CW power frame	≤ 150 W
Residual pulse energy (typ.)	350 μJ (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Residual pulse voltage (typ.)	650 V (test pulse 4 kV 1.2/50 μs; 2 kA 8/20 μs)
Surge current handling capability	30 kA single, 20 kA multiple (test pulse 8/20 μs)

Electrical bands

	Range 1
Frequency range	0 MHz ... 2000 MHz

**COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 3 GHz (Platform 3000),
with GDT 230 V**

3402.17.3003

Electrical bands

	Range 1
Return loss typical	≥ 26 dB
Insertion loss	≤ 0.2 dB
Power avg. / peak	≤ 150 W / -

Electrical remarks

DC current	6 A
Gas tube	Yes DC, GDT included, replaceable, 9071.99.0547 (230 V)

Mechanical data

Weight	159 g
Mating cycles	500

Environmental data

Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	IP67
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. D
Moisture resistance according	MIL-STD-202, Method 106

Ordering Information Table

Item number	Item description
85027390	3402.17.3003

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P42810 / Date of publication: 31.10.2024 / uncontrolled copy