

COAXIAL ADAPTER, N Quick-mate, 50 Ohm, plug / jack (male / female)

33_N-Q50-0-4/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
N Quick-mate	plug (male)	HUBER+SUHNER Quick-mate
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
N Quick-mate		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 5 GHz	29.4 dB	1.07
5 GHz ... 8 GHz	20.1 dB	1.22
8 GHz ... 11 GHz	16.5 dB	1.35

COAXIAL ADAPTER, N Quick-mate, 50 Ohm, plug / jack (male / female)

33_N-Q50-0-4/133_N

Mechanical data	
Weight	0.0372 kg
Mating cycles	500

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22660297	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22660297	33_N-Q50-0-4/133_NE	Single

Additional Information	
Remarks	Durability of QUICK MATE interface: 1000 matings

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2199 / Date of publication: 12.07.2025 / uncontrolled copy