

COAXIAL ADAPTER, N - QN, 50 Ohm, plug / jack (male / female)

33_N-QN-U50-1/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
not defined	plug (male)	
QN	jack (female)	QN QLF compliant

Interface and material data		
not defined		
Piece parts	Material	Plating
Centre contact	Bronze	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
QN		
Piece parts	Material	Plating
Centre contact	Bronze	SUCOPRO Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data	
Weight	0.0171 kg
Mating cycles	100

COAXIAL ADAPTER, N - QN, 50 Ohm, plug / jack (male / female)

33_N-QN-U50-1/133_N

Environmental data

Operation temperature	-40 °C ... 85 °C
-----------------------	------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
23033735	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description	Packaging type
23033735	33_N-QN-U50-1/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P2196 / Date of publication: 12.07.2025 / uncontrolled copy