

## COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 2.5 GHz, with SEMPER GDT 90 V

3402.26.0006-EX

### Properties

- Broadband frequency operation from DC to 2.5 GHz
- Gas discharge tube replaceable and included
- DC/AC remote powering via coaxial same cable
- Surge current handling capability 30 kA once and 20 kA multiple
- Semper self-extinguishing functionality included



CE UK  
CA

### Product configuration

Main path connectors	Port 1: unprotected, TNC jack (female) Port 2: protected, TNC jack (female)
Mounting and grounding	MH25 (bulkhead mounting)
Side of bulkhead	protected side
Capsule holder with chain	YES
EMP can be install reversed	YES

### Interface and material data

Housing material / plating	Brass / SUCOPLATE (R) Plating
Center contact, material / plating	Port 1: Copper Beryllium Alloy / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

### Electrical data

Impedance	50 Ω
Frequency frame	0 MHz to 2500 MHz
Return loss typical	≥ 20 dB
Insertion loss typical	≤ 0.2 dB
CW power frame	≤ 26 W
DC current	≤ 2.5 A at 48 V ≤ 4 A at 27 V ≤ 6 A at 24 V ≤ 13 A at 17 V
Turn-off time	20 sec. typically at 2.0 A and 25°C ambient temperature < 40 sec. typically below 1 A and 25°C ambient temperature
Recovery time	7 sec. at 25°C ambient temperature

**COAXIAL SURGE PROTECTOR DEVICE, GDT technology up to 2.5 GHz, with SEMPER GDT  
90 V**

3402.26.0006-EX

**Electrical data**

Residual pulse energy (typ.)	250 µJ (test pulse 4 kV 1.2/50 µs; 2 kA 8/20 µs)
Residual pulse voltage (typ.)	550 V (test pulse 4 kV 1.2/50 µs; 2 kA 8/20 µs)
Surge current handling capability	30 kA single, 20 kA multiple (test pulse 8/20 µs)

**Electrical remarks**

DC supply voltage	48 V
DC current	2.5 A
Gas tube	Yes DC, GDT included, replaceable, 9071.99.0648 (SEMPER, 90 V)

**Mechanical data**

Weight	119 g
Mating cycles	500

**Environmental data**

Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Ingress protection (IP Rating)	Mated / IP65, according to IEC 60529
Thermal shock according	MIL-STD-202, Method 107, Cond. B
Vibration according	MIL-STD-202, Method 204, Cond. D
Moisture resistance according	MIL-STD-202, Method 106

**Ordering Information Table**

Item number	Item description
84027271	3402.26.0006-EX

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P2002 / Date of publication: 29.10.2024 / uncontrolled copy