

COAXIAL ADAPTER, PC 7 - N, 50 Ohm, plug / jack (male / female)
33_PC7-N-50-1/1--_U

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
PC 7	plug (male)	IEEE STD 287_ANSI C 16.43
N-precision	jack (female)	IEC 60169-16_MIL-STD-348A/402_CECC 22210

Interface and material data		
PC 7		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	Air Dielectric - Bead - PPH	
Coupling nut	Brass	SUCOPLATE (R) Plating
N-precision		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	Air Dielectric - Bead - PPH	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz
VSWR	DC - 18 GHz (≤ 1.02 + 0.002 f GHz)

Mechanical data	
Weight	0.0474 kg
Mating cycles	500

COAXIAL ADAPTER, PC 7 - N, 50 Ohm, plug / jack (male / female)

33_PC7-N-50-1/1--_U

Environmental data	
Operation temperature	-55 °C ... 70 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22543547	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22543547	33_PC7-N-50-1/1--_UE	Single

Additional Information	
Remarks	Operating specification acc. IEEE Std 287: temperature 13 °C to 33 °C

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2175 / Date of publication: 12.07.2025 / uncontrolled copy