

COAXIAL ADAPTER, QLA-01 - BNC, X Ohm, plug / jack (male / female)

33_QLA-BNC-01-1/1--_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials

**Product configuration**

Interface type	Gender	Standard
QLA-01	plug (male)	NIM-CAMAC-Standard CD/N549
BNC	jack (female)	IEC 61169-8_MIL-STD-348A/301_CEEC 22120

Interface and material data

QLA-01		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data

Interface frequency	1.4 GHz
---------------------	---------

Mechanical data

Weight	0.0085 kg
Mating cycles	500

Environmental data

Operation temperature	-55 °C ... 150 °C
-----------------------	-------------------

COAXIAL ADAPTER, QLA-01 - BNC, X Ohm, plug / jack (male / female)

33_QLA-BNC-01-1/1--_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22640029	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22640029	33_QLA-BNC-01-1/1--_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2172 / Date of publication: 12.07.2025 / uncontrolled copy