


COAXIAL ADAPTER, SMB, 50 Ohm, Bulkhead, jack / jack (female / female)

34_SMB-50-0-3/111_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration

Interface type	Gender	Standard
SMB	jack (female)	IEC 60169-10_MIL-STD-348A/311_CECC 22130
SMB	jack (female)	IEC 60169-10_MIL-STD-348A/311_CECC 22130

Interface and material data

SMB		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)
SMB		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (without Nickel underplating)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Gasket	NR (Natural Rubber)	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

COAXIAL ADAPTER, SMB, 50 Ohm, Bulkhead, jack / jack (female / female)

34_SMB-50-0-3/111_N

Electrical Data (frequency related)			
Frequency range		Return loss	VSWR
0 GHz ... 4 GHz		18 dB	1.3
Mechanical data			
Weight		0.0022 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-20 °C ... 125 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22641380	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22641380	34_SMB-50-0-3/111_NE		Single
Additional Information			
Remarks		Hermetically sealed: leak rate <= 10^-6 Torr l/s (atm cc/s)	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2082 / Date of publication: 12.07.2025 / uncontrolled copy