


COAXIAL SURGE PROTECTOR DEVICE, Slim Line GDT technology

3406.19.0004

Properties

- Slim in-line design
- Broadband operation from DC up to 5.8 GHz
- DC continuity for remote powering
- Permanently installed gas discharge tube
- RF power up to 60W max.



Product configuration	
Main path connectors	Port 1: unprotected, SMA plug (male) Port 2: protected, SMA jack (female)
Mounting and grounding	MH3 (bulkhead mounting)
Side of bulkhead	protected side
Inline design	YES
EMP can be install reversed	YES

Interface and material data	
Housing material / plating	Brass / Silver / Gold Plating
Center contact, material / plating	Port 1: Brass / Gold Plating (without Nickel underplating) Port 2: Copper Beryllium Alloy / Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Frequency frame	0 MHz to 5800 MHz
Return loss typical	18.5 dB
Insertion loss typical	0.2 dB
CW power frame	60 W
Static spark voltage	200 V, +/- 25 % (@ 100 V/s)
Residual pulse energy (typ.)	250 μ J (test pulse 4 kV 1.2/50 μ s; 2 kA 8/20 μ s)
Surge current handling capability	10 kA single, 5 kA multiple (test pulse 8/20 μ s)

Electrical bands		
	Range 1	Range 2
Frequency range	0 MHz ... 5600 MHz	5600 MHz ... 5800 MHz
Return loss typical	20 dB	18.5 dB
Insertion loss	0.2 dB	0.2 dB

COAXIAL SURGE PROTECTOR DEVICE, Slim Line GDT technology

3406.19.0004

Electrical remarks			
DC supply voltage		48 V	
DC current		2 A	
Gas tube		Yes DC, GDT included, not replaceable	
Mechanical data			
Weight		24 g	
Mating cycles		500	
Environmental data			
Operation temperature		-40 °C ... 85 °C	
Storage temperature		-40 °C ... 85 °C	
Ingress protection (IP Rating)		IP20	
Thermal shock according		MIL-STD-202, Method 107, Cond. B	
Vibration according		MIL-STD-202, Method 204, Cond. D	
Moisture resistance according		MIL-STD-202, Method 106	
Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23026259	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Comment			
		Waterproof degree for unprotected side in mated condition: IP65 acc. IEC 60529.	
Ordering Information Table			
Item number		Item description	
23026259		3406.19.0004	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1971 / Date of publication: 28.02.2025 / uncontrolled copy