

COAXIAL ADAPTER, BNC, 75 Ohm, T-style, 1 plug (male), 2 jacks (female)

43_BNC-75-0-1/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration

Interface type	Gender	Standard
BNC	jack (female)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120
BNC	plug (male)	Compatible with IEC 61169-8_MIL-STD-348A/301_CECC 22120

Interface and material data

BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
BNC		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Washer	Copper Beryllium Alloy	SUCOPLATE (R) Plating

Electrical data

Impedance	75 Ω
Interface frequency	1 GHz

COAXIAL ADAPTER, BNC, 75 Ohm, T-style, 1 plug (male), 2 jacks (female)

43_BNC-75-0-1/133_N

Mechanical data	
Weight	0.0186 kg
Mating cycles	500

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22541049	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22541049	43_BNC-75-0-1/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1911 / Date of publication: 12.07.2025 / uncontrolled copy