

COAXIAL ADAPTER, QLA-01, X Ohm, T-style, 1 plug (male), 2 jacks (female)

43_QLA-01-0-1/112_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
QLA-01	jack (female)	NIM-CAMAC-Standard CD/N549
QLA-01	plug (male)	NIM-CAMAC-Standard CD/N549

Interface and material data		
QLA-01		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor		Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
QLA-01		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	Nickel Plating

Electrical data	
Interface frequency	1.4 GHz

Mechanical data	
Weight	0.0071 kg
Mating cycles	10000

Environmental data	
Operation temperature	-55 °C ... 150 °C

COAXIAL ADAPTER, QLA-01, X Ohm, T-style, 1 plug (male), 2 jacks (female)
43_QLA-01-0-1/112_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22640032	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22640032	43_QLA-01-0-1/112_NE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1909 / Date of publication: 12.07.2025 / uncontrolled copy