

COAXIAL ADAPTER, 4.3-10, 50 Ohm, Bulkhead, jack / jack (female / female)

34_4310-50-0-1/003_-

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration

Interface type	Gender	Standard
4.3-10	jack (female)	IEC 61169-54
4.3-10	jack (female)	IEC 61169-54

Interface and material data

4.3-10		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer conductor	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
4.3-10		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Silver Plating
Outer conductor	Bronze	Silver Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Electrical data

Impedance	50 Ω
Interface frequency	12 GHz

Mechanical data

Weight	0.076 kg
Mating cycles	100

COAXIAL ADAPTER, 4.3-10, 50 Ohm, Bulkhead, jack / jack (female / female)

34_4310-50-0-1/003_-

Environmental data	
Operation temperature	-55 °C ... 90 °C
Ingress protection (IP Rating)	Mated / IP68

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85064169	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
85064169	34_4310-50-0-1/003_-E	Single

Additional Information	
Remarks	PIM typ. -166 dBc at 2 x 20 W / 43 dBm

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2132 / Date of publication: 12.07.2025 / uncontrolled copy