

COAXIAL ADAPTER, MCX, 50 Ohm, Bulkhead, jack / jack (female / female)

34_MCX-50-0-2/111_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
MCX	jack (female)	IEC 60169-36_CEEC 22220
MCX	jack (female)	IEC 60169-36_CEEC 22220

Interface and material data		
MCX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)
MCX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

COAXIAL ADAPTER, MCX, 50 Ohm, Bulkhead, jack / jack (female / female)

34_MCX-50-0-2/111_N

Electrical Data (frequency related)			
Frequency range		Return loss	VSWR
0 GHz ... 1.5 GHz		30 dB	1.06
1.5 GHz ... 6 GHz		20 dB	1.22
Mechanical data			
Weight		0.0021 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-55 °C ... 155 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22649868	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22649868	34_MCX-50-0-2/111_NE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2115 / Date of publication: 12.07.2025 / uncontrolled copy