

IMPEDANCE MATCHING PAD, N
6001.17.A

Properties

- Low insertion loss
- High repeatability
- Low return loss



Interface and material data	
Interface side 1	N / plug (male)
Standard side 1	IEC 60169-16_MIL-STD-348A/304_CECC 22210
Center contact, material / plating	Brass / Gold Plating (Nickel underplated)
Outer contact, material / plating	Brass / SUCOPLATE (R) Plating
Body, material / plating	Brass / SUCOPLATE (R) Plating
Insulator, material	PFA / PTFE
Coupling nut, material / plating	Brass / SUCOPLATE (R) Plating
Interface side 2	jack (female)
Standard side 2	IEC 60169-16_MIL-STD-348A/304_CECC 22210
Outer contact, material / plating	Brass / SUCOPLATE (R) Plating
Body, material / plating	Brass / SUCOPLATE (R) Plating
Insulator, material	PFA / PTFE

Electrical data	
Impedance nominal	50 Ω (side 1) / 75 Ω (side 2)
Frequency frame	0 GHz to 1 GHz
Attenuation nominal	5.7 dB
Voltage division	50 Ω to 75 Ω 4 dB / 75 Ω to 50 Ω 7.5 dB

Electrical bands		
	Band 1	Band 2
Frequency range	0 GHz ... 0.5 GHz	0.5 GHz ... 1 GHz
VSWR max side 1	1.15	1.25
VSWR max side 2	1.15	1.25

IMPEDANCE MATCHING PAD, N
6001.17.A

Electrical remarks			
Power rating		0.7 W at 40 °C ambient temperature. Linearly derated to 0 W at 125 °C ambient temperature.	
Mechanical data			
Weight		0.0665 kg	
Compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22642807	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number		Item description	
22642807		6001.17.A	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1816 / Date of publication: 28.02.2025 / uncontrolled copy