

COAXIAL ADAPTER, MMBX - QMA, 50 Ohm, Bulkhead, jack / jack (female / female)

34_MMBX-QMA-50-2/1--_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
MMBX	jack (female)	HUBER+SUHNER-MMBX
QMA	jack (female)	QMA QLF compliant

Interface and material data		
MMBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer conductor	Brass	SUCOPRO / Gold Plating
Body	Brass	SUCOPRO / Gold Plating
Insulator	LCP (Liquid crystal polymer)	
QMA		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	12.4 GHz

Mechanical data	
Weight	0.0054 kg
Mating cycles	100

COAXIAL ADAPTER, MMBX - QMA, 50 Ohm, Bulkhead, jack / jack (female / female)

34_MMBX-QMA-50-2/1--_N

Environmental data

Operation temperature	-40 °C ... 85 °C
-----------------------	------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
84071040	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description	Packaging type
84071040	34_MMBX-QMA-50-2/1--_NY	Tray

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2112 / Date of publication: 12.07.2025 / uncontrolled copy