

COAXIAL TERMINATION, 50 Ohm, TNC, plug (male)

6506.26.0002

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power



Product configuration		
Interface	Gender	Standard
TNC	plug (male)	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 6 GHz
VSWR	1.25
Return loss	19.1 dB

Electrical Data (frequency related)		
Frequency range	VSWR max	Return loss
0 GHz to 2 GHz	1.1	
2 GHz to 4 GHz	1.2	
4 GHz to 6 GHz	1.25	

Electrical Data (power)	
Average power	6 W at 40 °C ambient temperature. Linearly derated to W at 130 °C ambient temperature.
Peak power	1000 W, 5 μs pulse width, 0.05 % duty cycle

Interface and material data		
Interface	TNC / plug (male)	
Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Aluminium	

COAXIAL TERMINATION, 50 Ohm, TNC, plug (male)
6506.26.0002

Interface and material data		
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Piece parts	Material	Plating

Mechanical data	
Weight	0.062 kg

Environmental data	
Operation temperature	-40 °C ... 130°C

Ordering Information Table	
Item number	Item description
22649996	6506.26.0002

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1722 / Date of publication: 09.11.2023 / uncontrolled copy