

COAXIAL ADAPTER, N, 50 Ohm, Bulkhead, jack / jack (female / female)

34_N-50-0-1/133_U

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	12.4 GHz
VSWR	DC - 12.4 GHz ($\leq 1.06 + 0.17 f \text{ GHz}$)

COAXIAL ADAPTER, N, 50 Ohm, Bulkhead, jack / jack (female / female)

34_N-50-0-1/133_U

Mechanical data	
Weight	0.0477 kg
Mating cycles	500

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22651817	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22651817	34_N-50-0-1/133_U	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2107 / Date of publication: 12.07.2025 / uncontrolled copy