

COAXIAL TERMINATION, 75 Ohm, MCX, jack (female)

65_MCX-75-0-31/111_N

Properties

- Various bandwidth
- Impedance matched
- Standard or precision types
- Low and medium power

**Product configuration**

Interface	Gender	Standard
MCX	jack (female)	HUBER+SUHNER - MCX75

Electrical data

Impedance	75Ω
Operating frequency	0 GHz ... 2 GHz
VSWR	1.3
Return loss	17.7 dB

Electrical Data (frequency related)

Frequency range	VSWR max	Return loss
0 GHz to 1 GHz	1.2	
1 GHz to 2 GHz	1.3	

Electrical Data (power)

Average power	0.5 W at 30 °C ambient temperature. Linearly derated to W at 130 °C ambient temperature.
---------------	--

Interface and material data

Interface	MCX / jack (female)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Piece parts	Material	Plating

COAXIAL TERMINATION, 75 Ohm, MCX, jack (female)
65_MCX-75-0-31/111_N

Mechanical data	
Weight	0.0022 kg
Environmental data	
Operation temperature	-40 °C ... 130°C

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1771 / Date of publication: 09.11.2023 / uncontrolled copy