

COAXIAL ADAPTER, N - SMB, 50 Ohm, Bulkhead, jack / jack (female / female)

34_N-SMB-50-1/1--_U

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration

Interface type	Gender	Standard
N	jack (female)	IEC 61169-16_MIL-STD-348A/304_CECC 22210
SMB	jack (female)	IEC 60169-10_MIL-STD-348A/311_CECC 22130

Interface and material data

N		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
SMB		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer conductor	Brass	Gold Plating (without Nickel underplating)
Body		Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

Electrical data

Impedance	50 Ω
Interface frequency	4 GHz

COAXIAL ADAPTER, N - SMB, 50 Ohm, Bulkhead, jack / jack (female / female)
34_N-SMB-50-1/1--_U

Electrical Data (frequency related)			
Frequency range		Return loss	VSWR
0 GHz ... 4 GHz		20 dB	1.22
Mechanical data			
Weight		0.005 kg	
Mating cycles		500	
Environmental data			
Operation temperature		-65 °C ... 165 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22642272	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22642272	34_N-SMB-50-1/1--_UE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2098 / Date of publication: 12.07.2025 / uncontrolled copy