

COAXIAL ADAPTER, SHV, 50 Ohm, Bulkhead, jack / jack (female / female)

34_SHV-50-0-5/133_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration

Interface type	Gender	Standard
SHV	jack (female)	IEC 60498_MIL-STD-348A/314
SHV	jack (female)	IEC 60498_MIL-STD-348A/314

Interface and material data

SHV		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PS (Polystyrene)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
SHV		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PS (Polystyrene)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating

Electrical data

Impedance	50 Ω
Interface frequency	0.3 GHz

COAXIAL ADAPTER, SHV, 50 Ohm, Bulkhead, jack / jack (female / female)

34_SHV-50-0-5/133_N

Mechanical data	
Weight	0.0252 kg
Mating cycles	500

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22544583	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
22544583	34_SHV-50-0-5/133_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2092 / Date of publication: 12.07.2025 / uncontrolled copy