

COAXIAL ADAPTER, QLA-01, X Ohm, T-style, 1 plug (male), 2 jacks (female), asymmetric
45_QLA-01-0-1/112_N

Properties

- Wide range of different configurations
- Most common interfaces available
- Accurate transitions
- Effective and reliable interconnection solutions
- Appropriate materials



Product configuration		
Interface type	Gender	Standard
QLA-01	plug (male)	NIM-CAMAC-Standard CD/N549
QLA-01	jack (female)	NIM-CAMAC-Standard CD/N549

Interface and material data		
QLA-01		
Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	Nickel Plating
QLA-01		
Piece parts	Material	Plating
Centre contact	Bronze	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Electrical data	
Interface frequency	1.4 GHz

Mechanical data	
Weight	0.0076 kg
Mating cycles	10000

COAXIAL ADAPTER, QLA-01, X Ohm, T-style, 1 plug (male), 2 jacks (female), asymmetric

45_QLA-01-0-1/112_N

Environmental data

Operation temperature	-55 °C ... 150 °C
-----------------------	-------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
22640033	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description	Packaging type
22640033	45_QLA-01-0-1/112_NE	Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1903 / Date of publication: 12.07.2025 / uncontrolled copy