


COAXIAL CONNECTOR, SMPM, 50 Ohm, Straight PCB plug (male), full detent

81_SMPM-S50-0-F7/111_N

Properties

- Best performance-to-price ratio
- Excellent RF performance up to 65 GHz
- Small size, compact form factor
- Snap-on coupling mechanism with full detent and smooth bore
- Board-to-board solutions with bullets for axial and radial float



Product configuration

Interface type	Gender	Standard
SMPM	plug	MIL-STD-348B

Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	65 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 12 GHz	26 dB	1.11
12 GHz ... 18 GHz	20 dB	1.22
18 GHz ... 26 GHz	15 dB	1.43

Mechanical data

Weight	0.24 g
Mating cycles	100
Board mounting type	surface mount
Height above PCB HA	3.4 mm

Engagement / Disengagement force

	Engagement	Disengagement
Interface class	Full detent	Full detent

COAXIAL CONNECTOR, SMPM, 50 Ohm, Straight PCB plug (male), full detent
81_SMPM-S50-0-F7/111_N

Engagement / Disengagement force

	Engagement	Disengagement
Interface force typical	20 N	29 N

Environmental data

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

Material compliance

Item number	Directive / Regulation	Rating	Exemptions / Details
85248367	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	6c CAS: 7439-92-1 Lead
85248326	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	6c CAS: 7439-92-1 Lead

Ordering Information Table

Item number	Item description	Packaging type
85248367	81_SMPM-S50-0-F7/111_NE	Single
85248326	81_SMPM-S50-0-F7/111_NM	Tape and Reel

Additional Information

Remarks	The values provided are typical and may vary depending on factors such as the mating connector, PCB (layout), and assembly condition.
---------	---

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P61091 / Date of publication: 04.12.2025 / uncontrolled copy