


COAXIAL CONNECTOR, BMA, 50 Ohm, Straight PCB jack (female)

82_BMA-50-0-1/111_N

Properties

- Offers a range of floating configurations
- High reliability and ease of assembly
- Intermatable with the OSP connectors series
- Applicable in frequencies up to 18 GHz



Product configuration		
Interface type	Gender	Standard
BMA	jack	IEC 60169-33_MIL-STD-348A/321

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

Electrical data	
Impedance	50 Ω
Interface frequency	18 GHz

Mechanical data	
Weight	0.001 kg
Mating cycles	1000
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	9.5 mm
Height of stand off HS	0 mm

Engagement / Disengagement force		
	Engagement	Disengagement
Interface force min		2 N
Interface force max	14 N	

COAXIAL CONNECTOR, BMA, 50 Ohm, Straight PCB jack (female)

82_BMA-50-0-1/111_N

Environmental data			
Operation temperature		-65 °C ... 125 °C	
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
22645631	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
22645631	82_BMA-50-0-1/111_NE		Single
Additional Information			
Remarks		PCB connector without stand-offs	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1359 / Date of publication: 12.07.2025 / uncontrolled copy