

2-Way Reactive Power Splitter

5501.17.0030

Properties

- Reactive power splitter in 380 MHz till 2700 MHz band
- -150 dBc PIM @ 2x43 dBm
- 300 W power handling
- N female interface
- IP67 rating



Ports		
Port designation	Interface	Gender
Input 1	N	jack (female)
Output 1	N	jack (female)
Output 2	N	jack (female)

Electrical bands	
	Signal band 1
Frequency range	0.38 GHz ... 2.7GHz
Return loss input port	≥ 19 dB
Splitter loss	3 dB
Insertion loss	< 0.1 dB
Amplitude tracking btw. output port	0.3 dB
Composit power max	300 W
Intermodulation distortion	< -150 dBc
@ 2 x carrier power	43 dBm

Electrical Data (impedance)	
Characteristic impedance	50 Ω

Mechanical data	
Weight	0.33 kg
Width	28.5 mm
Height	267 mm
Depth	28.5 mm
Housing material and surface treatment	Aluminium / Black paint
Remarks	Mounting: 2 Clips supplied

2-Way Reactive Power Splitter

5501.17.0030

Environmental data	
Environment (application)	Indoor/Outdoor
Operation temperature	-35 °C ... 85 °C
Storage temperature	-35 °C ... 85 °C
Transport temperature	-35 °C ... 85 °C
Ingress protection (IP Rating)	IP67

Ordering Information Table	
Item number	Item description
85029258	5501.17.0030

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1876 / Date of publication: 25.04.2025 / uncontrolled copy