

**Tapper 4.8 dB**

5501.31.0003

**Properties**

- The innovative asymmetric design ensures an excellent input VSWR and coupling flatness across the band
- The lightweight design allows easy attachment to a wall using the supplied bracket
- Designed with only a few solder joints and an air dielectric, loss is minimized and reliability enhanced
- It supports public safety and cellular bands, as well as Wi-Fi 2.4

**Ports**

Port designation	Interface	Gender
Main line in	4.3-10	jack (female)
Main line out	4.3-10	jack (female)
Tap port, 4.8 dB	4.3-10	jack (female)

**Electrical bands**

	<b>Band 1</b>	<b>Band 2</b>
Frequency range	350 MHz ... 960MHz	1710 MHz ... 2700GHz
Return loss	≥ 17.6 dB	≥ 17.6 dB
Tapp loss	4.8 dB	4.8 dB
Insertion loss	≤ 1.3 dB	≤ 1.3 dB
Composit power max	300 W	300 W
Peak envelope power	2000 W	2000 W
Intermodulation distortion	≤ -161 dBc	≤ -161 dBc
@ 2 x carrier power	43 dBm	43 dBm

**Electrical Data (impedance)**

Characteristic impedance	50 Ω
--------------------------	------

**Tapper 4.8 dB**

5501.31.0003

**Mechanical data**

Weight	0.42 kg
Width	89 mm
Height	32 mm
Depth	32 mm
Housing material and surface treatment	Aluminium / Black paint

**Environmental data**

Environment (application)	Indoor/Outdoor
Operation temperature	-40 °C ... 75 °C
Storage temperature	-40 °C ... 75 °C
Transport temperature	-40 °C ... 75 °C
Ingress protection (IP Rating)	IP67

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1873 / Date of publication: 25.04.2025 / uncontrolled copy