

COAXIAL CONNECTOR, SK, 50 Ohm, Edge mount PCB jack (female)

82_SK-S50-0-200/199_N

Properties

- Non-magnetic
- Excellent return loss
- Mechanical intermateable with SMA and PC 3.5 (3.5 mm standard)
- Operating frequency up to 40 GHz

**Product configuration**

Interface type	Gender	Standard
SK	jack	MIL-STD-348B

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Stainless steel	Passivated (Plating)
Insulator	PEI (Polyether-imide)	

Electrical data

Impedance	50 Ω
Interface frequency	40 GHz

Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 40 GHz	20 dB	1.22

Mechanical data

Weight	0.002 kg
Mating cycles	500

Environmental data

Operation temperature	-40 °C ... 165 °C
-----------------------	-------------------

COAXIAL CONNECTOR, SK, 50 Ohm, Edge mount PCB jack (female)
82_SK-S50-0-200/199_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85221621	RoHS 2011/65/EU and (EU) 2015/863	Compliant without exemption	
	REACH 1907/2006 Article 33 SVHC	Free of SVHC >0,1%	

Ordering Information Table	
Item number	Item description
85221621	82_SK-S50-0-200/199_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P40880 / Date of publication: 12.07.2025 / uncontrolled copy