

COAXIAL FIXED ATTENUATOR, 50 Ohm, 10 dB, QMA

6810_QMA-50-2/133_N

Properties

- Wide range of interfaces
- Various bandwidth to improve the impedance matching between subsystems of its waveform
- Used in many test and measurement and communication applications.



Product configuration		
Interface	Gender	Standard
QMA	plug (male)	QMA QLF compliant
QMA	jack (female)	QMA QLF compliant

Electrical data	
Impedance	50Ω
Operating frequency	0 GHz ... 6 GHz
Attenuation nominal	10 dB
VSWR	1.2
Return loss	20.8 dB

Electrical Data (frequency related)		
Frequency range	Attenuation deviation	VSWR max
0 GHz to 6 GHz	+/- 0.5 dB	1.2

Electrical Data (power)	
Average power	2 W at 25 °C ambient temperature. Linearly derated to 0.2 W at 100 °C ambient temperature.
Peak power	250 W, 5 μs pulse width, 0.4 % duty cycle

Interface and material data		
Interface	QMA / plug (male)	
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Brass	Tri-metal Plating
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Brass	Tri-metal Plating
Interface	QMA / jack (female)	

COAXIAL FIXED ATTENUATOR, 50 Ohm, 10 dB, QMA
6810_QMA-50-2/133_N

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer conductor	Brass	Tri-metal Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Mechanical data	
Weight	0.007 kg

Environmental data	
Operation temperature	-55 °C ... 125 °C

Ordering Information Table	
Item number	Item description
85177168	6810_QMA-50-2/133_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver:
Facts and figures herein are for information only and do not represent any warranty of any kind.

DOCUMENT PIM-P1617 / Date of publication: 21.11.2024 / uncontrolled copy