


COAXIAL CONNECTOR, N, 50 Ohm, Edge mount PCB jack (female)
92_N-50-0-6/111_N

Properties

- Screwed coupling mechanism for sturdy and reliable connection
- IP rating (interface, mated) IP67
- Interface dimensions according IEC/MIL



Product configuration		
Interface type	Gender	Standard
N	jack	IEC 61169-16_MIL-STD-348A/304_CECC 22210

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE (Polytetrafluoroethylene)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Mechanical data	
Weight	0.03 kg
Mating cycles	500
Board mounting type	edge mount

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, N, 50 Ohm, Edge mount PCB jack (female)

92_N-50-0-6/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84057317	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
84057317	92_N-50-0-6/111_NY	Tray

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1147 / Date of publication: 12.07.2025 / uncontrolled copy