


# COAXIAL CONNECTOR, SMPM, 50 Ohm, Straight PCB plug (male) with ground pin in-hole and SMT Signal pin, full detent

95\_SMPM-50-0-F2/111\_N

## Properties

- Best performance-to-price ratio
- Excellent RF performance up to 65 GHz
- Small size, compact form factor
- Snap-on coupling mechanism with full detent and smooth bore
- Board-to-board solutions with bullets for axial and radial float



## Product configuration

Interface type	Gender	Standard
SMPM	plug	MIL-STD-348B

## Interface and material data

Piece parts	Material	Plating
Centre contact	Brass	SUCOPRO Plating
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE (Polytetrafluoroethylene)	

## Electrical data

Impedance	50 Ω
Interface frequency	65 GHz

## Electrical Data (frequency related)

Frequency range	Return loss	VSWR
0 GHz ... 18 GHz	25 dB	1.12
18 GHz ... 40 GHz	17 dB	1.33
40 GHz ... 65 GHz	12 dB	1.67

## Mechanical data

Weight	0.34 g
Mating cycles	100
Board mounting type	pin-in-hole / SMT
Number of printlegs	4
Height above PCB HA	4.15 mm

**COAXIAL CONNECTOR, SMPM, 50 Ohm, Straight PCB plug (male) with ground pin in-hole and SMT Signal pin, full detent**

95\_SMPM-50-0-F2/111\_N

**Engagement / Disengagement force**

	<b>Engagement</b>	<b>Disengagement</b>
Interface class	Full detent	Full detent
Interface force typical	20 N	29 N

**Environmental data**

Operation temperature	-65 °C ... 165 °C
-----------------------	-------------------

**Material compliance**

Item number	Directive / Regulation	Rating	Exemptions / Details
85270010	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	6c CAS: 7439-92-1 Lead
85244553	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

**Ordering Information Table**

Item number	Item description	Packaging type
85270010	95_SMPM-50-0-F2/111_NE	Single
85244553	95_SMPM-50-0-F2/111_NM	Tape and Reel

**Additional Information**

Remarks	The values provided are typical and may vary depending on factors such as the mating connector, PCB (layout), and assembly condition.
---------	---

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.  
DOCUMENT PIM-P60543 / Date of publication: 04.12.2025 / uncontrolled copy