


COAXIAL CONNECTOR, MCX, 50 Ohm, Straight PCB jack (female)

82_MCX-50-0-17/111_N_-1

Properties

- Small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available

**Product configuration**

Interface type	Gender	Standard
MCX	jack	IEC 60169-36_CEEC 22220

Interface and material data

Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Electrical data

Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data

Weight	0.0007 kg
Mating cycles	500
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	6 mm
Height of stand off HS	0 mm

Engagement / Disengagement force

	Engagement	Disengagement
Interface force min		8 N
Interface force max	25 N	20 N

COAXIAL CONNECTOR, MCX, 50 Ohm, Straight PCB jack (female)

82_MCX-50-0-17/111_N_-1

Environmental data	
Operation temperature	-65 °C ... 165 °C

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
23006209	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead

Ordering Information Table		
Item number	Item description	Packaging type
23006209	82_MCX-50-0-17/111_NH-1	Bulk 100 pcs

Additional Information	
Remarks	PCB connector without stand-offs

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1345 / Date of publication: 12.07.2025 / uncontrolled copy