

SENCITY® Rail Antenna
K702121

Properties

- Railway rooftop antenna for 450 to 470 MHz
- Rugged design, meets EN 50155 Railway Standard
- Fire retardant according to EN 45545-2
- Contains a heavy-duty fiberglass radome
- Works also on non-metallic surfaces



Electrical bands	
	Band 1
Name	Tetra
Frequency	450 MHz ... 470 MHz
Impedance	50 Ω
VSWR	1.6
Gain	3 dBi
Ambient Temperature	25 °C
Electrical remarks	
Remarks	Indicated VSWR values are valid for a metallic ground plane of 1M x 1M or larger.
Ports	
	Port 1
Port name	Tetra
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes
Connections	
	Port 1
Port name	Tetra
Band 1	☒

SENCITY® Rail Antenna

K702121

Mechanical data	
Weight	0.8 kg
Dimensions	355 mm x 145 mm x 80 mm (Height x Width x Depth)
	Packaging size (outside): 151 x 90 x 415 mm
Remarks	Flange: Aluminum. Radiator: Copper. Sealing: Neoprene and EPDM.


Interface and material data	
Radome material	Fiberglass
Radome colour	Grey
Back plate/base plate material	Aluminum
Back plate/base plate colour	Grey

Environmental data	
Operation temperature	-40 °C ... 85 °C
Storage temperature	-40 °C ... 85 °C
Environment (application)	Outdoor
Ingress protection (IP Rating)	Mated / IP66
Flammability rating	EN 45545-2

Environmental remarks	
Environmental tests: EN 50155:2018-05	

SENCITY® Rail Antenna
K702121

Outline drawing



HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P1029 / Date of publication: 12.08.2024 / uncontrolled copy